


Digital Oscilloscope



Trigger Level: -10, 0, 10 AC DC Auto One-Shot Cursors Source: A B C D	Channel A Position: 110, 120, 130 AC DC GND OFF Invert A+B Scale: 0.5, 0.2, 0.1, 50, 20, 10, 5, 2, 1 V 1 mV	Channel C Position: -110, -100, -90 AC DC GND OFF Invert C+D Scale: 0.5, 0.2, 0.1, 50, 20, 10, 5, 2, 1 V 5 mV
Horizontal Source: A B C D Position: 80, 870, 880, 850 Scale: 0.50, 0.1, 0.05, 50, 20, 10, 5, 2, 1, 200, 50 mS 50u μS	Channel B Position: -30, -20, -10, 0 AC DC GND OFF Invert Scale: 0.5, 0.2, 0.1, 50, 20, 10, 5, 2, 1 V 1 mV	Channel D Position: -130, -120, -110 AC DC GND OFF Invert Scale: 0.5, 0.2, 0.1, 50, 20, 10, 5, 2, 1 V 5 mV